

## Model 420XL

# Pressure Vacuum Breaker Assembly with Integral Anti-Freeze Relief Valve

## **Application**

Ideal for use where Lead-Free\* valves are required. Designed for installation on potable water lines to protect against backsiphonage of contaminated water into the potable water supply. Supplied with an integral anti-freeze relief valve to reduce the risk of valve damage under intermittent, non-seasonal freezing conditions. Designed for use under continuous pressure. Assembly shall provide protection where a potential health hazard exists.

## **Standards Compliance**

- ASSE® Listed 1020
- IAPMO® Listed
- CSA® Certified
- Approved by the Foundation for Cross Connection Control and Hydraulic Research at the University of Southern California
- Certified to NSF/ANSI 372\* by IAPMO R&T \*(0.25% MAX. WEIGHTED AVERAGE LEAD CONTENT)

#### **Materials**

Main valve body Low Lead Cast Bronze

ASTM B 584

Elastomers Silicone (FDA Approved)

Buna Nitrile (NSF Listed)

Polymers Polypropylene (FDA Approved)

Delrin™ (NSF Listed)

Noryl™ (NSF Listed)

Springs Stainless Steel, 300 Series

## **Features**

Sizes: 3/4", 1"

Maximum working water pressure 175 PSI
Maximum working water temperature 140°F
Hydrostatic test pressure 350 PSI
Threaded connections ANSI B1.20.1

Integral anti-freeze relief valve

Replaceable thermoplastic modular cartridge



## **Options**

(Suffixes can be combined)

with full port QT ball valves (standard)

□ PF - with Z-Bite<sup>™</sup> push fit connections\*

☐ PR - with Z-Press<sup>™</sup> press fit connections\*

\*Fittings ship in box with valve and must be threaded into valve by hand on site.


#### **Accessories**

☐ Repair kit (complete)

Repair kit (rubber only)

☐ Repair kit (freeze kit)

Water hammer arrester (Model 1250XL)



## Dimensions & Weights (do not include pkg.)

MODEL CIZE		DIMENSIONS (approximate)										
	MODEL SIZE		А		В		С		WEIGHT			
	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kg		
	3/4	20	6 3/4	172	4 1/4	108	3 13/16	97	4	1.8		
	1	25	7 15/16	202	4 15/16	125	4 1/2	114	5	2.3		


Zurn Industries, LLC | Wilkins

1747 Commerce Way, Paso Robles, CA U.S.A. 93446 Ph. 855-663-9876, Fax 805-238-5766 In Canada | **Zurn Industries Limited** 

3544 Nashua Drive, Mississauga, Ontario L4V 1L2 Ph. 905-405-8272, Fax 905-405-1292

Rev. D Date: 6/15 Document No. BF-420XL Product No. Model 420XL

## MODEL 420XL 3/4" & 1" (STANDARD & METRIC)





♦ Rated Flow (Established by approval agencies)

## **Typical Installation**

Local codes shall govern installation requirements. Unless otherwise specified, the assembly shall be installed in accordance with the manufacturers' instructions and the latest edition of the Uniform Plumbing Code. The assembly shall be mounted at a minimum of 12" (305mm) above the highest piping or outlet downstream of the device. Install with adequate drain and sufficient side clearance for testing and maintenance. The installation shall be made so that no part of the unit can be submerged. A pressure vacuum breaker cannot be installed where back-pressure could occur or where spillage of water from vent could cause damage.

Capacity thru Schedule 40 Pipe										
Pipe size	5 ft/sec	7.5 ft/sec	10 ft/sec	15 ft/sec						
1/8"	1	1	2	3						
1/4"	2	2	3	5						
3/8"	3	4	6	9						
1/2	5	7	9	14						
3/4"	8	12	17	25						
1"	13	20	27	40						
1 1/4"	23	35	47	70						
1 1/2"	32	48	63	95						
2"	52	78	105	167						





## **OUTDOOR INSTALLATION**

#### INDOOR INSTALLATION

### **Specifications**

The Pressure Vacuum Breaker shall be certified to NSF/ANSI 372, ASSE® Listed 1020, and supplied with full port ball valves. The main body shall be low lead bronze (ASTM B 584), the loaded-air inlet shall use a silicone elastomer spring and seat disc. The assembly shall include an integral relief valve. The entire assembly shall be accessible for maintenance and testing without removing the device from the line. The Pressure Vacuum Breaker shall be a ZURN WILKINS Model 420XL.

In Canada | Zurn Industries Limited

<sup>3544</sup> Nashua Drive, Mississauga, Ontario L4V 1L2 Ph. 905-405-8272, Fax 905-405-1292